


SCHOTT RG830, 50mm Sq., 2mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock #14-536 3-5 DAYS

-

1

+

A\$124.00

ADD TO CART

Qty 1-10
A\$124.00
Qty 11+
A\$121.60
Volume Pricing
Request Quote

Get Product Downloads
Dimensions (mm): 50.0 x 50.0
Cut-On Wavelength (nm): 830.00 ±9
Density (g/cm³):

2.94
Glass/Filter Number: SCHOTT RG830
Length (mm): 50.00
Coating: Uncoated
Color: Black
Passband Limit 1 λ_{p1} (nm): 950
Passband Limit 2 λ_{p2} (nm): 1100
Index of Refraction n_d : 1.56
Spectral Transmittance t_p (%): 97
Stopband Limit λ_s (nm): 670
Surface Quality: 60-40
Transformation Temperature (°C): 554
Thickness (mm): 2.00 ±0.2
Type: Longpass Filter
Wavelength: IR
Width (mm): 50.00
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d : 0.91
Bevel: Protective as needed

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View