



SCHOTT UG11, 12.5mm Dia., 2mm Thick, Colored Glass Bandpass Filter

See More by [SCHOTT Optical Components](#)



Stock #16-372 3-5 DAYS

[Additional Bandwidths](#)

1

A\$75.20

ADD TO CART

Qty 1-10
A\$75.20
Qty 11+
A\$65.60
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
12.50

Center Wavelength CWL (nm):
325.00

Density (g/cm³): 2.92
Glass/Filter Number: SCHOTT UG11
Coating: Uncoated
Color: Black
Index of Refraction n_d: 1.56
Surface Quality: 60-40
Transformation Temperature (°C): 545
Thickness (mm): 2.00 ±0.2
Type: Bandpass Filter
Wavelength: UV
Bevel: Protective as needed

Regulatory Compliance

Certificate of Conformance: View
--