

# SCHOTT UG11, 12.5mm Dia., 3mm Thick, Colored Glass Bandpass Filter

See More by [SCHOTT Optical Components](#)



Stock #16-388 3-5 DAYS

[Additional Bandwidths](#)

1

A\$75.20

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-10                      |
| A\$75.20                      |
| Qty 11+                       |
| A\$65.60                      |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads

Diameter (mm):  
12.50

Center Wavelength CWL (nm):  
325.00

|                                                            |
|------------------------------------------------------------|
| <b>Density (g/cm³):</b><br>2.92                            |
| <b>Glass/Filter Number:</b><br><a href="#">SCHOTT UG11</a> |
| <b>Coating:</b><br>Uncoated                                |
| <b>Color:</b><br>Black                                     |
| <b>Index of Refraction n<sub>d</sub>:</b><br>1.56          |
| <b>Surface Quality:</b><br>60-40                           |
| <b>Transformation Temperature (°C):</b><br>545             |
| <b>Thickness (mm):</b><br>3.00 ±0.2                        |
| <b>Type:</b><br>Bandpass Filter                            |
| <b>Wavelength:</b><br>UV                                   |
| <b>Bevel:</b><br>Protective as needed                      |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |