

SCHOTT VG20, 12.5mm Dia., 1mm Thick, Colored Glass Bandpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#16-365**

3-5 DAYS

[Additional Bandwidths](#)

-

1

+

A\$75.20

ADD TO CART

Qty 1-10

A\$75.20

Qty 11+

A\$65.60

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
12.50

Center Wavelength CWL (nm):
500.00

Density (g/cm³): 2.85
Glass/Filter Number: SCHOTT VG20
Coating: Uncoated
Color: Green
Index of Refraction n_d: 1.54
Surface Quality: 60-40
Transformation Temperature (°C): 390
Thickness (mm): 1.00 ±0.1
Type: Bandpass Filter
Wavelength: UV-VIS
Bevel: Protective as needed

Regulatory Compliance

Certificate of Conformance: View
--