



SCHOTT VG9 12.5mm Dia., 1mm Thick Colored Glass Bandpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#16-369** 3-5 DAYS

[Additional Bandwidths](#)

− 1 +

A\$65.60

ADD TO CART

Qty 1-10

A\$65.60

Qty 11+

A\$59.20

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
12.50

Center Wavelength CWL (nm):
525.00

Density (g/cm³): 2.87
Glass/Filter Number: SCHOTT VG9
Coating: Uncoated
Color: Green
Index of Refraction n_d: 1.55
Surface Quality: 60-40
Transformation Temperature (°C): 462
Thickness (mm): 1.00 ±0.1
Type: Bandpass Filter
Wavelength: VIS
Bevel: Protective as needed

Regulatory Compliance

Certificate of Conformance: View
--