

[See all 5 Products in Family](#)

## Standard, Premier Laser Diode Detector



Premier Laser Diode Detector

Stock **#58-760** **2 In Stock**

⊖ 1 ⊕ A\$200<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-9	A\$200.00 each
Qty 10+	A\$190.00 each
Need More?	<a href="#">Request Quote</a>

**Note:** This item requires accessories for use | [Learn More](#)

### Product Downloads

### General

Standard **Type:**

### Physical & Mechanical Properties

15.00 **Diameter (mm):**

54.50 **Length (mm):**

50.00 **Weight (g):**

Anodized Aluminum **Construction:**

## Optical Properties

20.00 **Relative Ambient Light Rejection (dB):**

## Electrical

>60 **AC & DC S/N Ratio for 1mW Input (dB):**

750.00 **AC Output Frequency Response (kHz):**

1.00 **AC Output Sensitivity @ 650nm (V/mW):**

<20 **Current (mA):**

5 - 10 DC **Voltage (V):**

## Hardware & Interface Connectivity

4 pin JST **Connector:**

**Power Supply:**  
Power Supply Required and Sold Separately:  
USA: [#59-099](#)  
Europe: Not Available  
Japan: [#59-099](#)  
Korea: Not Available  
China: [#59-099](#)

4 input/output leads **Electrical Leads/ Pin Connections:**

## Environmental & Durability Factors

-10 to +70 **Operating Temperature (°C):**

90% RH **Operating Humidity:**

-40 to +85 **Storage Temperature (°C):**

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 240:**

## Product Details

- Designed for Use with the [Premier Laser Diodes](#)
- Wide Acceptance Angle
- Ideal for Particle Detection and Densitometry

Designed for use with the [Premier Laser Diodes](#), these detectors have a wide acceptance angle of 160 degrees and an amplification system, which makes them very versatile for indoor and outdoor applications. Condition monitoring such as fog and smoke, particle detection and densitometry are a few uses for the detector. The optional mount is a heavy duty clamp with a series of threaded holes for versatile integration at any angle. There is also a removable cover which exposes an M12 screw thread used for mounting.

A power supply, sold separately, is required for operation. We recommend [#59-099](#) 5V Universal Power Supply.