

TECHSPEC® 48mm, T-Mount Ring Mount, M6 Tapped Hole



Stock **#63-978** **20+ In Stock**

⊖ 1 ⊕ **A\$166⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1-4	A\$166.40 each
Qty 5-9	A\$147.36 each
Qty 10-25	A\$136.48 each
Need More?	Request Quote

Product Downloads

General

Post Mounting Adapter

Function:

Physical & Mechanical Properties

Construction:
Black Anodized Aluminum (6061 T6)

Outer Diameter (mm):
68.0

Thickness (mm):
20.00

Inner Diameter (mm):
48.0

Threading & Mounting

Thread Type:
T-Mount

Mounting Flat to Center (mm):
31.83

Compatible Post:
M6 x 1.0

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Reach 209:
[Compliant](#)

Certificate of Conformance:
[View](#)

Product Details

- Allow for Post Mounting C, S, and T-Mount Tube System Assemblies
- 1/4-20 or M6 Tapped Mounting Options
- Black Anodized Aluminum Construction

TECHSPEC® C, S, and T-Mount Ring Mounts feature a screw closure and accept 30mm, 16mm, and 48mm outer diameter tubes and barrels, respectively. Ring mounts are available with either 1/4-20 or M6 tapped mounting threads with a flat mounting surface to facilitate mounting to optical bench posts. These mounts are compatible with a wide variety of Edmund Optics optomechanical components utilizing C, S, or T-Mount threads. TECHSPEC C, S, and T-Mount Ring Mounts are ideal for quickly integrating C, S, or T-Mount tube assemblies into any benchtop system. A black anodized construction reduces reflections within a system.

Technical Information

