

Ti:Sapphire Variable Ultrafast Pulse Compressor, 780 - 830nm



Stock **#26-397** [CONTACT US](#)

-

1

+

A\$12,974.40

ADD TO CART

Qty 1+
A\$12,974.40
Volume Pricing
Request Quote

Get Product Downloads

Polarization: p
Dimensions (inches): 9 x 8 x 4
Wavelength Range (nm): 780 - 830
GDD Specification (fs²): -10400 to -2600
Input Beam Diameter, 1/e² (mm): 2 (maximum)

Minimum Efficiency (%):
97.60

GDD Increment (fs²):
-2600

Regulatory Compliance

RoHS:
Compliant

Certificate of Conformance:
[View](#)