

## Tripod Adapter For Go and Go-X Series Models, (20 mm hole spacing)



Stock #29-174 **1 In Stock**

- 1 + A\$59<sup>20</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	A\$59.20 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### Regulatory Compliance

Certificate of Conformance:

[View](#)

## Product Details

- Up to 12.3 MP Resolution
- USB and GigE Versions Available
- Longest Industry Warranty (6 Years)

JAI® Go-X Series Cameras are designed to be compact, industrial grade, reliable cameras with excellent image quality. Featuring industrial grade shock and vibration ratings (80G/10G) as well as excellent thermal dissipation, these cameras are ideal for factory floors and assembly lines. Designed with a variety of capabilities, these cameras are capable of region-of-interest (ROI), blemish compensation with shading correction, and 8, 10, and 12-bit output. JAI®

Go-XSeries Cameras are available in resolutions ranging from 2.3 to 12.3MP with both USB or Gigabit Ethernet (GigE) outputs. Downloadable software is [available](#) for both GigE and USB options.

---

;