

[All Products](#) / [Cameras](#) / [USB Cameras](#) / [IDS Imaging uEye CP/XCP/SE USB3 Cameras](#)

[See all 58 Products in Family](#)

IDS Imaging U3-3280CP-M-GL 2/3" Monochrome USB3 Camera

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye+ USB3 Camera, CP Model (Front)



Stock **#16-533** 3-5 DAYS

[Similar Cameras](#)

- 1 +

A\$2,060.80

ADD TO CART

Qty 1+
A\$2,060.80
Volume Pricing
Request Quote

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Video Output:
USB 3.0

Type:
Monochrome Camera

Manufacturer: IDS Imaging
Mounting Threads: 1/4-20 with Tripod Mount Adapter #35-088
Image Buffer: 128MB
Camera Family: uEye+ CP
Model Number: U3-3280CP-M-GL Rev.2.2
Imaging Sensor: Sony IMX264
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 2/3"
Resolution (MegaPixels): 5.01
Pixels (H x V): 2,448 x 2,048
Pixel Size, H x V (µm): 3.45 x 3.45
Sensing Area, H x V (mm): 8.45 x 7.07
Frame Rate (fps): 36.00
Pixel Depth: 12 bit
Exposure Time: 27µs - 2s
Connector: USB 3.0, Micro-B
Power Supply: Power over USB
Power Consumption (W): 1.6 - 3.1
GPIOs: 2 Flash Output, 2 Trigger Input, 2 GPIO, 1 Output Supply Voltage, 1 Ground
Synchronization: Hardware Trigger (GPIO)
Dimensions (mm): 29.0 x 29.0 x 29.0 (excludes connectors and lens mount)
Weight (g): 47
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): Not Specified
Operating Temperature (°C): 0 to +55
Storage Temperature (°C): -20 to +60
GPIO Connector Type: 8-pin Hirose (HR25)
Machine Vision Standard: USB3 Vision v1.0

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
Reach 233: Contains SVHC(s)

