

TECHSPEC[®] VIS (UV/IR Cut) M40.5 x 0.50 High Performance Machine Vision Filter



TECHSPEC[®] High Performance Mounted Machine Vision Filters

Stock #89-798 3-5 DAYS

-

1

+

A\$360.00

ADD TO CART

Qty 1-9

A\$360.00

Qty 10+

A\$330.88

Volume Pricing

[Request Quote](#)

Get Product Downloads

Blocking Wavelength Range (nm):

200-370, 750-1100

Clear Aperture CA (mm):

36.5

Coating:

Hard Coated

Filter Thread:

M40.5 x 0.50
Color: VS
Center Wavelength CWL (nm): 548.00
Construction: Mounted in Black Anodized Ring
Full Width-Half Max FWHM (nm): 290.00
Mount Thickness (mm): 5.0
Mount Thickness Including Threads (mm): 7.0
Note: OD ≥3.0 @ 750 - 1100nm OD ≥4.0 @ 200 - 370nm
Optical Density OD (Average): ≥3.0
Outer Diameter (mm): 42.0
Substrate Thickness (mm): 1.75 ±0.10
Type: Mounted Imaging Filter
Average Transmission (%): ≥90
Environmental Durability: Humidity per MIL-STD-810H, Section 507.6 Temperature per MIL-STD-810H, Section 501.7 and 502.7
Physical Durability: Adhesion per MIL-PRF-13830B, Section C.4.5.12 Moderate abrasion per MIL-PRF-13830B, Section C.4.5.11 Cleaning per MIL-C-48497A Section 4.5.4.2

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View