

UV-VIS and IR High Power Laser Beam Visualizer



High Power Laser Beam Visualizers

Stock #11-449 3-5 DAYS

− 1 +

A\$185.60

ADD TO CART

Qty 1-24

A\$185.60

Qty 25+

A\$167.04

Volume Pricing

[Request Quote](#)

Get Product Downloads



Active Area Diameter (mm):
35

Outer Diameter (mm):
42

Dimensions (mm):
Disk: 42 Dia.
Wand: 130 Length

Wavelength: UV, VIS, IR
Damage Threshold, By Design: ☐ Typical: 1 J/cm ² @ 10ns
Emission Color: Red
Stimulation Range: 190 - 1090nm, 1470 - 1600nm

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
