


Variable Frequency Targets 5-200 lp/mm



Stock **#43-488** CLEARANCE **1 In Stock**

-

1

+

A\$1,440^{.00}

ADD TO CART

Volume Pricing	
Qty 1-4	A\$1,440.00 each
Qty 5+	A\$1,368.80 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties	
25.4 x 39.37	Pattern Size (mm):
2 x 2	Dimensions (inches):
1.50	Thickness (mm):
Beveled	Edges:

Flatness (mm):

0.00254

Optical Properties

	Coating:
Vacuum deposited durable chromium	
	Substrate:
Float Glass	

	Optical Density OD (Average):
≥3.0	
	Surface Quality:
40-10	

Regulatory Compliance

	RoHS 2015:
Compliant	
	Certificate of Conformance:
View	
	REACH 241:
Compliant	

Product Details

- 5 lp/mm to 120 lp/mm or 5 lp/mm to 200 lp/mm
 - 1mm Wide Step Size
 - 5 lp/mm Step Increments
 - Used to Calibrate Video Systems
 - Inspect Unknown Resolutions
- Variable frequency targets are excellent for evaluating resolution, field distortion, and parfocal stability.