

TECHSPEC® VIS (400-700nm) OD 4.0 10nm Bandpass Filter Kit, 25mm Dia



Stock **#88-299** 3-5 DAYS

⊖ 1 ⊕ **A\$1,968.00**

ADD TO CART

Qty 1+
A\$1,968.00

Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
25.00

Optical Density OD (Average):
≥4.0

Full Width-Half Max FWHM (nm):
10.00

Filters Included :
CWL: [400nm](#), [450nm](#), [500nm](#), [550nm](#), [600nm](#),
[650nm](#), [700nm](#)

Coating:
Hard Coated

Type: Bandpass Filter
Typical Applications: Chemical Analysis, Laser Diode Cleanup
Wavelength: VIS
Number of Filters: 7
Environmental Durability: Humidity: MIL-STD 810.F, Method 507.4
Physical Durability: Adhesion: MIL-C-48497A, 3.4.1.1 Abrasion: MIL-C-48497A, 3.4.1.3 Temperature: MIL-C-48497A, 3.4.2.1 Cleaning: MIL-C-48497A, 3.4.2.3

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
