

# Vis M37.5 x 0.50 Mounted Machine Vision Filter



Mounted Machine Vision Filters

Stock #21-676 3-5 DAYS

- 1 + **A\$222.40**

ADD TO CART

Qty 1-9

A\$222.40

Qty 10+

A\$212.48

Volume Pricing

[Request Quote](#)

Get Product Downloads

**Blocking Wavelength Range (nm):**

366 -380, 720-1100

**Clear Aperture CA (mm):**

32.50

**Coating:**

Hard Coated

**Filter Thread:**

|                                                        |
|--------------------------------------------------------|
| M37.5 x 0.50                                           |
| <b>Color:</b><br>Vis                                   |
| <b>Center Wavelength CWL (nm):</b><br>550.00           |
| <b>Construction:</b><br>Mounted in Black Anodized Ring |
| <b>Full Width-Half Max FWHM (nm):</b><br>300.00        |
| <b>Mount Thickness (mm):</b><br>5.2                    |
| <b>Mount Thickness Including Threads (mm):</b><br>7.0  |
| <b>Outer Diameter (mm):</b><br>39.50                   |
| <b>Substrate Thickness (mm):</b><br>1.3                |
| <b>Type:</b><br>Mounted Imaging Filter                 |
| <b>Minimum Transmission (%):</b><br>≥85                |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |