

Vis M55 x 0.75 Mounted Machine Vision Filter



Mounted Machine Vision Filters

Stock #21-489 3-5 DAYS

- 1 +

A\$297.60

ADD TO CART

Qty 1-9

A\$297.60

Qty 10+

A\$283.20

Volume Pricing

[Request Quote](#)

Get Product Downloads

Blocking Wavelength Range (nm):

355 -380, 720-1100

Clear Aperture CA (mm):

50.00

Coating:

Hard Coated

Filter Thread:

M55 x 0.75
Color: Vis
Center Wavelength CWL (nm): 550.00
Construction: Mounted in Black Anodized Ring
Full Width-Half Max FWHM (nm): 300.00
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0
Outer Diameter (mm): 57.00
Substrate Thickness (mm): 1.3
Type: Mounted Imaging Filter
Minimum Transmission (%): ≥85

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View