

VZM™ 450 Zoom Imaging Lens



Stock #52-347 CLEARANCE 3-5 DAYS

1

A\$1,203.12

ADD TO CART

Qty 1+

A\$1,203.12

Volume Pricing

[Request Quote](#)

Get Product Downloads

Length excluding Threads (mm):
234.80

Horizontal Field of View, 1/2" Sensor:
8.5 - 1.4mm

Horizontal Field of View, 2/3" Sensor:
11.7 - 2.0mm

Filter Thread:
None

Maximum Diameter (mm): 56.5
Weight (g): 580.00
Working Distance Tolerance (mm): ±3
Resolution, Object Space: 30 - 144
Resolution, Image Space: 40 - 32
Zoom Ratio: 6.4:1
Type: Zoom Lens
Primary Magnification PMAQ: 0.75X - 4.5X
Maximum Sensor Format: 2/3"
Working Distance (mm): 90.00
Mount: C-Mount
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View