

[All Products](#) / [Imaging Lenses](#) / [Zoom Lenses](#) / [VZM™ Zoom Imaging Lenses](#)

[See all 17 Products in Family](#)

VZM™ 450i Zoom Imaging Lens



Stock **#54-671** CLEARANCE 3-5 DAYS

1

A\$1,203.12

ADD TO CART

Qty 1+

A\$1,203.12

Volume Pricing

[Request Quote](#)

Get Product Downloads

Length excluding Threads (mm):
239.00

Horizontal Field of View, 1/2" Sensor:
8.8 - 1.4mm

Horizontal Field of View, 2/3" Sensor:
12.0 - 1.9mm

Filter Thread:
M22.5 x 0.50

Maximum Diameter (mm): 35.00
Weight (g): 405.00
Working Distance Tolerance (mm): +3/-4
Resolution, Object Space: 30 - 144
Resolution, Image Space: 40 - 32
Zoom Ratio: 6.4:1
Type: Zoom Lens
Primary Magnification PMAQ: 0.7X - 4.5X
Maximum Sensor Format: 2/3"
Working Distance (mm): 90.00
Mount: C-Mount
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View