

[See all 13 Products in Family](#)

White 225mm Compact Light w/ Multi-Drive™



225mm Compact Light



Stock **#23-946** [CONTACT US](#)

- 1 + **A\$2,232⁰⁰**

ADD TO CART

Volume Pricing

Qty 1+	A\$2,232.00 each
Need More?	Request Quote

Product Downloads

General

JWL225-MD-WHI **Model Number:**

LED Illuminator **Type of Illumination:**

Smart Vision Lights LLC **Manufacturer:**

Ring Light **Geometry:**

Constant or Strobed **Illumination Mode:**

Physical & Mechanical Properties

Dimensions (mm):
230 W x 142 H x 45D (60.40 D Including Connector)

Weight (g):
1496.85

Active Area (mm):
144.50W x 56.5H

Optical Properties

Color:
White

Working Distance (mm):
500 - 2,000

Electrical

Strobe Duration (µs):
30 - ∞

Hardware & Interface Connectivity

Connector:
5-pin M12 connector

Input Voltage (V):
24 VDC ± 5%

Threading & Mounting

Mount:
T-Slot for M6 Nut

Environmental & Durability Factors

Operating Temperature (°C):
-10° to +40°

Environmental Rating:
IP65

Regulatory Compliance

Certificate of Conformance:
[View](#)

Product Details

- Direct Connect and Control via Camera's Trigger Output
- Built-In Multi-Drive™ Technology
- T-Slots for Mounting

Smart Vision Lights Compact Ring Lights are IP65-rated brightfield lights featuring a working distance of 500-mm to 2000-mm that can be directly connected to a camera for control via the trigger output. Built-in Multi-Drive™ technology, which offers both continuous operation and OverDrive™ mode, delivers up to 6 times the continuous power with a low-latency response and fast strobe durations down to 10mS. These lights feature a batwing design that illuminates a larger area than built-in lighting systems and produces a greater light output making them ideal to use alongside polarizers, diffusers, and other optical elements that reduce light output. Smart Vision Lights Illumination products offer an industry-leading 10-year limited warranty.