

White, Coaxial LED Spot Light

See More by [Advanced Illumination](#)



Stock #66-861 3-5 DAYS

-

1

+

A\$811.20

ADD TO CART

Qty 1+

A\$811.20

Volume Pricing

[Request Quote](#)

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color:
White

Model Number:
SL112-WHI-IC

Operating Temperature (°C):
0 to 60

Weight (g):
42.5

LED Lifetime (hours): 50,000
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Light Distribution (%): ±10
Number of LEDs: 1 High Brightness
Length of Cable (m): 1.5
Type of Illumination: LED Illuminator
Manufacturer: Advanced Illumination
Geometry: Spot Light
Illumination Mode: Constant

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Contains SVHC(s)
