

White, Strobed, 6" High Brightness LED Line Light

See More by [Advanced Illumination](#)



Stock #83-295 [CONTACT US](#)

⊖ 1 ⊕ **A\$1,113.60**

ADD TO CART

Qty 1+
A\$1,113.60

Volume Pricing
Request Quote

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color: White
Operating Lifetime (hours): 50,000
Model Number: LL17406-WHI-I3S
Mount: T-Slot for M6 Nut

Operating Voltage (V): 24 DC
Dimensions (mm): 171.3 L x33.8 Wx27.9 D
Weight (g): 300.00
Working Distance (inches): 12.00
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Length of Cable (m): 2
Maximum Trigger Frequency (Hz): 30.00
Strobe Duration (µs): 30 - 300
Type of Illumination: LED Illuminator
Note: Optional Manual Intensity Adjustment #86-887 and #89-555 are Available
Manufacturer: Advanced Illumination
Geometry: Line Light
Illumination Mode: Strobed

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Contains SVHC(s)