

Zero Aperture, 25mm Max. Aperture, Iris Diaphragm



Stock #53-907 3-5 DAYS

- 1 +

A\$97.60

ADD TO CART

Qty 1-9

A\$97.60

Qty 10+

A\$86.56

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
0.00

Maximum Aperture (mm):
25.0

Outer Diameter (mm): 38.0
Construction: Black Anodized Aluminum, Black Spring Steel Leaves, Stainless Steel Pins
Lever Diameter (mm): 3.00
Lever Length (mm): 12.80
Number of Leaves: Two Sets of 7
Spacing of Leaf Layers (mm): 2.5
Thickness (mm): 6.10

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)