

Zero Aperture, 25mm Max. Aperture, Mounted Iris Diaphragm



Stock #62-654 3-5 DAYS

- 1 + **A\$147.20**

ADD TO CART

Qty 1-9
A\$147.20
Qty 10+
A\$130.40
Volume Pricing
Request Quote

Get Product Downloads

Type: Mounted
Minimum Aperture (mm): 0.00
Maximum Aperture (mm): 25.0

Outer Diameter (mm): 52.0
Construction: Black Anodized Aluminum, Black Spring Steel Leaves, Stainless Steel Pins
Lever Diameter (mm): 3.00
Lever Length (mm): 12.80
Number of Leaves: Two Sets of 7
Spacing of Leaf Layers (mm): 2.4
Thickness (mm): 9.50

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 235: Contains SVHC(s)