

Zero Aperture, 37mm Max. Aperture, Mounted Iris Diaphragm



Stock #62-655 3-5 DAYS

-

1

+

A\$176.00

ADD TO CART

Qty 1-9

A\$176.00

Qty 10+

A\$155.36

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type:
Mounted

Minimum Aperture (mm):
0.00

Maximum Aperture (mm):
37.0

Outer Diameter (mm): 67.0
Construction: Black Anodized Aluminum, Black Spring Steel Leaves, Stainless Steel Pins
Lever Diameter (mm): 3.00
Lever Length (mm): 12.60
Number of Leaves: Two Sets of 8
Spacing of Leaf Layers (mm): 2.7
Thickness (mm): 9.50

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 235: Contains SVHC(s)