

Zinc Selenide, 12.7mm, Uncoated, ISP Optics IR Right Angle Prism | ZC-RP-12

See More by [ISP Optics](#)



Infrared (IR) Right Angle Prisms

Stock **#19-708** 3-5 DAYS

-

1

+

A\$2,000.00

ADD TO CART

Qty 1-5
A\$2,000.00
Qty 6+
A\$1,600.00
Volume Pricing
Request Quote

Get Product Downloads



Coating:

Uncoated

Substrate: ☐

Zinc Selenide (ZnSe)

Surface Quality:

60-40
Type: Right Angle Prism
Dimensional Tolerance (mm): ±0.25
Angle Tolerance (arcmin): ±10
Clear Aperture (%): 85.00
Length of Hypotenuse (mm): 18.00
Length of Legs (mm): 12.70
Image Orientation: Left-Handed
Ray Deviation (°): 90
Wavelength Range (nm): 600 - 18000
Wavelength Range (µm): 0.6 - 18
Surface Flatness (P-V): 2λ
Model Number: ZC-RP-12

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View