600nm CWL, 10nm FWHM, 12.5mm Mounted Diameter

Stock **#65-648** 3-5 DAYS

Additional Bandwidths

- 1 + **A$142.40**

ADD TO CART

Qty 1-9
A$142.40

Qty 10+
A$128.48

Volume Pricing
Request Quote

Get Product Downloads

CUSTOM OPTIONS

Diameter (mm):	12.50 +0.0/-0.2
Angle of Incidence (°):	0
Optical Density OD (Average):	≥3.0

Clear Aperture CA (mm):
9.0

Center Wavelength CWL (nm):
600.00 ±2

Center Wavelength CWL Tolerance (nm):
±2

Full Width-Half Max FWHM (nm):
10.00 ±2

Full Width-Half Max FWHM Tolerance (nm):
±2

Minimum Transmission (%):
≥45

Operating Temperature (°C):
-50 to +75

Coating:
Traditional Coated

Surface Quality:
80-50

Thickness Tolerance (mm):
±0.1

Type:
Bandpass Filter

Typical Applications:
Clinical Chemistry

Blocking Wavelength Range (nm):
200 - 1200

Construction:
Mounted in Black Anodized Ring

Mount Thickness (mm):
7.5 ±0.1

Regulatory Compliance

RoHS 2015:
Compliant

Reach 219:
Compliant

Certificate of Conformance:
View