TECHSPEC® 20mm Square, Uncoated, B270 Window

See More by SCHOTT Optical Components



Stock **#64-087** 3-5 DAYS

1 **A$51.20**

ADD TO CART

Qty 1-5
A$51.20

Qty 6+
A$40.80

Volume Pricing
Request Quote

Get Product Downloads

Abbe Number (v_d):
58.3

Bevel:
Protective as needed

Clear Aperture CA (mm):
18.00 x 18.00

Dimensions (mm):
20.00 x 20.00

Thickness (mm):
2.00

Coating:
Uncoated

Coefficient of Thermal Expansion CTE (10^{-6}/°C):
9.4 (+20 to +300°C)

Density (g/cm^3):
2.56

Edges:
Fine Ground

Index of Refraction n_d:
1.523

Knoop Hardness (kg/mm^2):
500

Poisson's Ratio:
0.22

Substrate:
B270

Surface Flatness (P-V):
1λ

Surface Quality:
60-40

Type:
Protective Window

Wavelength Range (nm):
360 - 2700

Young's Modulus (GPa):
71.5

Length (mm):
20.00

Width (mm):
20.00

Regulatory Compliance

RoHS 2015:
Compliant

Certificate of Conformance:
View

Reach 235:
Compliant