25.4mm Dia. x -76.2mm FL, Uncoated, ISP Optics Calcium Fluoride (CaF>sub>2) PCV Lens | CF-PC-25-76

See More by ISP Optics

Stock **#24-783** CONTACT US

- 1 + **A$248.00**

ADD TO CART

Qty 1-9
A$248.00

Qty 10+
A$223.20

Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
25.40 +0.00/-0.13

Effective Focal Length EFL (mm):
-76.20 @ 5µm

Substrate:
Calcium Fluoride (CaF_2)

f/#:
3.00

Numerical Aperture NA:
0.17

Coating:
Uncoated

Type:
Plano-Concave Lens

Wavelength Range (nm):
300 - 8000

Bevel:
Protective bevel as needed

Center Thickness CT (mm):
2.00 ±0.20

Centering (arcmin):
<3

Clear Aperture CA (mm):
22.86

Edge Thickness ET (mm):
4.80

Focal Length Tolerance (%):
±2

Model Number:
CF-PC-25-76

Radius R_1 (mm):
-30.70

Surface Quality:
60-40

Irregularity (P-V) @ 632.8nm:
λ

Regulatory Compliance

RoHS 2015:
Compliant

Certificate of Conformance:
View