5° Diffusing Angle 25mm Dia Mounted

Stock **#47-994** 3-5 DAYS

- 1 + **A$288.00**

ADD TO CART

Qty 1-5
A$288.00

Qty 6+
A$244.80

Volume Pricing
Request Quote

Get Product Downloads

Angle Tolerance (°):
±1

Diffusing Angle (°):
5 (FWHM)

Clear Aperture CA (mm):
21.6

Diameter (mm):
25.00 ±0.1

Operating Temperature (°C):
-30 to +100 (Maximum of 240 Hours)

Substrate:
Polycarbonate

Thickness (mm):
2.60

Transmission (%):
>85

Type:
Holographic Diffuser

Wavelength Range (nm):
400 - 700

Construction:
Mounted

Damage Threshold, By Design:
0.22 J/cm^2 @ 1064nm, 10ns (typical)

Regulatory Compliance

RoHS 2015:
Compliant

Certificate of Conformance:
View

Reach 233:
Compliant