600 x 500mm, 1λ Retarder Film (WP560)



Retarder Film with protective film removed



Stock **#14-360** 3-5 DAYS

- 1 + **A$856.00**

ADD TO CART

Qty 1-10
A$856.00

Qty 11+
A$766.40

Volume Pricing
Request Quote

Get Product Downloads

Design Wavelength DWL (nm):
560

Substrate:
Polymer Film WP560

Length (mm):

600.00

Operating Temperature (°C):
-40 to +80

Retardance:
1λ

Dimensions (mm):
600.0 x 500.0

Thickness (mm):
0.15 ±0.015

Transmission (%):
>89

Type:
Retarder Film

Dimensional Tolerance (mm):
+0.0/-2.0

Construction:
Polarizing Film

Phase Shift (°):
360

Haze (%):
<1

Note:
Fast axis is indicated by a black stripe on the protective film. This film should be removed before use.

Wavelength Range (nm):
400 - 700

Heat Resistance (°C x Hours):
80 x 1000

Width (mm):
500.00

Retardation (nm):
560 ±10

Regulatory Compliance

RoHS 2015:
Compliant

Certificate of Conformance:
View

Reach 235:
Compliant