See all 10 Products in Family

Blue 200 x 200 Flat Dome Light

Effilux Flat Dome Lights

Stock **#22-107** CONTACT US

- 1 + **A$1,332.00**

ADD TO CART

Volume Pricing	
Qty 1+	**A$1,332.00** each
Need More?	Request Quote

Note: This item requires accessories for use | Learn More

Product Downloads

General

Model Number:	EFFI-FD-200-200-465
Type of Illumination:	LED Illuminator
Manufacturer:	Effilux
Geometry:	Flat Dome Light

Illumination Mode:
Constant

Physical & Mechanical Properties

Dimensions (mm):
239 x 239 x 43.2

Weight (g):
1900

Active Area (mm):
200 x 200

Optical Properties

Color:
Blue

Wavelength (nm):
465

Electrical

Power Consumption (W):
30

Hardware & Interface Connectivity

Input Voltage (V):
24

Power Supply:
Power Supply Required and Sold Separately:
USA: **#15-874**
Europe: **#15-875**
Japan: **#73-409**
Korea: **#73-409**
China: **#15-874**

Regulatory Compliance

RoHS 2015:
Compliant

Reach 224:
Compliant

Certificate of Conformance:
View

Product Details

- Dome Light Performance in a Flat Housing
- Integrated Analog Controller for Precise Intensity and Dimming
- Anti-Reflection System to Absorb Stray Light
- Continuous or Strobe mode

Effilux Flat Dome Lights achieve diffuse illumination similar to standard dome lights but with a thinner, more compact housing. These flat dome lights provide a large imaging area for increased depth of focus and field of view. The convenient integrated analog controller allows precise control of power and intensity without the need for additional components. Effilux Flat Dome Lights offer greater than 90% uniformity and feature an anti-reflection system that absorbs unwanted light. Flat Dome Lights are ideal for imaging textured, shiny, or uneven surfaces.

;