

**TECHSPEC®**

# 12.7mm Dia. Protected Aluminum Coated, Mounted Fused Silica Corner Cube Retroreflector



Mounted Fused Silica Corner Cube Retroreflectors

Stock **#15-818** **1 In Stock**

⊖ 1 ⊕ **A\$726<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1-5	<b>A\$726.40</b> each
Qty 6-25	<b>A\$580.80</b> each
Qty 26-49	<b>A\$545.60</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Retroreflector **Type:**

**Physical & Mechanical Properties**

**Diameter Tolerance (mm):**  
+0.0/-0.1

12.7	<b>Inner Diameter (mm):</b>
31.75	<b>Outer Diameter (mm):</b>
	<b>Housing Tolerance (mm):</b> Outer Diameter: +0/-0.5, Height: ±0.25

## Optical Properties

±5	<b>Beam Deviation (arcsec):</b>
Aluminum with protective overcoat	<b>Coating:</b>
<a href="#">Fused Silica</a> (Coming 7980)	<b>Substrate:</b> <input type="checkbox"/>
20-10	<b>Surface Quality:</b>
Left-Handed	<b>Image Orientation:</b>
Reflective Surfaces: $R_{avg} > 85\%$ FROM 400-700nm, @ 45° AOI	<b>Coating Specification:</b>
180	<b>Ray Deviation (°):</b>
400 - 700	<b>Wavelength Range (nm):</b>
0.20	<b>Power (fringes) @ 632.8nm:</b>
0.20	<b>Irregularity (fringes) @ 632.8nm:</b>

## Threading & Mounting

(2) 1/4-20 Tapped Holes	<b>Mounting Threads:</b>
-------------------------	--------------------------

## Regulatory Compliance


<a href="#">View</a>	<b>Certificate of Conformance:</b>
----------------------	------------------------------------

## Product Details

- 1/4-20 Tapped Holes for Easy Mounting
- Excellent Transmission in the UV
- Useful for Surveying and Alignment
- Also Available [Unmounted](#)


TECHSPEC® Mounted Fused Silica Corner Cube Retroreflectors are pre-mounted in anodized aluminum housings with two 1/4-20 tapped holes for easy integration into optical systems. Corner cube retroreflectors are designed to reflect any ray or beam entering the prism face, regardless of the orientation of the prism, back onto itself. Mirrors will only do this at a normal angle of incidence, making corner cube retroreflectors better suited for applications where precision alignment is difficult or time-consuming. TECHSPEC Mounted Fused Silica Corner Cube Retroreflectors are ideal for prototyping or research applications that require convenient, durable mounting solutions. These mounted retroreflectors provide excellent transmission in the UV.

## Technical Information



Stock No.	Inner Diameter ID	Outer Diameter OD	H	X
<a href="#">#15-817</a>	12.7	31.75	11.73	18.08
<a href="#">#15-818</a>	12.7	31.75	11.73	18.08
<a href="#">#15-819</a>	25.4	38.10	20.62	26.98
<a href="#">#15-820</a>	25.4	38.10	20.62	26.98

#15-821	50.8	63.50	39.95	46.30
#15-822	50.8	63.50	39.95	46.30



Units: mm