

## 25/25.4mm, Mounting Cell



25.4mm, Mounting Cell, #56-760

Stock **#56-760** 20+ In Stock

-

1

+

A\$43<sup>60</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | A\$43.60 each                 |
| Qty 10-25      | A\$39.36 each                 |
| Qty 26-49      | A\$37.44 each                 |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

|                 |  |
|-----------------|--|
| Type:           |  |
| Fixed           |  |
| Type of Optics: |  |
| Circular        |  |

Physical & Mechanical Properties

|                         |  |
|-------------------------|--|
| Construction:           |  |
| Black Anodized Aluminum |  |

|                       |                                           |
|-----------------------|-------------------------------------------|
| 3.2                   | Max. Thickness of Compatible Optics (mm): |
| 30.0                  | Cell Diameter (mm):                       |
| Threading & Mounting  |                                           |
| 25.0 - 25.4           | Size of Compatible Optics (mm):           |
| 5.0                   | Cell Thickness (mm):                      |
| Regulatory Compliance |                                           |
| Exempt                | RoHS 2015:                                |
| View                  | Certificate of Conformance:               |
| Contains SVHC(s)      | Reach 247:                                |

Product Details

• Allows Stacking of 3 or 5 Filters

• Black Anodized Aluminum

• **Posts** and **Post Holders** Required for Mounting

Fixed/Multiple Filter MOUNTS are ideal for use with neutral density filters in stacking applications. Mounting cell holds filter with diameter "F" in place with a retainer ring. Mounting cell sits securely in filter holder. Fixed/Multiple Filter MOUNTS can also hold unmounted filters with diameter "A". A filter holder and filter cell are required for a complete stacking system, such as the one illustrated in the product image. These mounts are constructed of black anodized aluminum and are optimal for mounting 3 or 5 circular optics.


**Posts** and **Post Holders** are required for mounting to a breadboard.

Technical Information


| Stock No. | A    | B    | C    | D   | No. of Slots | No. of Cell Slots |
|-----------|------|------|------|-----|--------------|-------------------|
| #55-006   | 30mm | 50mm | 34mm | 5mm | 4            | 3                 |
| #55-007   | 50mm | 70mm | 44mm | 5mm | 5            | 5                 |

| Stock No. | F      | G      | H    |
|-----------|--------|--------|------|
| #56-759   | 12.7mm | 10.2mm | 30mm |
| #55-008   | 25mm   | 22.5mm | 30mm |
| #56-760   | 25.4mm | 22.9mm | 30mm |
| #55-009   | 50mm   | 47mm   | 52mm |

Multiple Filter Holder



Mounting Cell



Units: mm