

[See all 24 Products in Family](#)

Allied Vision Manta G-895 1" Color CMOS Camera

See More by [Allied Vision](#)



Allied Vision Manta GigE Cameras (Front)



Stock **#36-179** **1 In Stock**

[Similar Cameras](#)

A\$3,136⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$3,136.00 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

Color Spectrum:

General

Color Camera Type:

Manta G-895 **Model Number:**

Allied Vision **Manufacturer:**

Manta **Camera Series:**

Physical & Mechanical Properties

71 x 44 x 29 (excludes connectors and lens mount) **Dimensions (mm):**

190 **Weight (g):**

Full **Housing:**

Sensor

128MB **Image Buffer:**

1" **Sensor Format:**

8.90 **Resolution (Megapixels):**

13.40 **Frame Rate (fps):**

4,112 x 2,176 **Pixels (H x V):**

3.45 x 3.45 **Pixel Size, H x V (µm):**

14.2 x 7.5 **Sensing Area, H x V (mm):**

Sony IMX267 **Imaging Sensor:**

Progressive Scan CMOS **Type of Sensor:**

Global **Shutter Type:**

8/12 bit **Pixel Depth:**

Auto Exposure **Exposure Time:**

71.9 **Dynamic Range (dB):**

GigE Vision v1.2, GenICam SFNC V1.2.1 **Machine Vision Standard:**

Electrical

3 (12VDC External Power Supply) **Power Consumption (W):**

Hardware & Interface Connectivity

GigE **Interface:**

GigE, RJ45 with Screw Locks **Connector:**

Power Supply Required and Sold Separately:
USA: [#15-281](#)
Europe: [#15-281](#)
Japan: [#15-281](#)
China: [#15-281](#) **Power Supply:**

2 opto-isolated inputs, 2 opto-isolated outputs **GPIOs:**

Hardware Trigger (GPIO) or Software Trigger **Synchronization:**

Back Panel **Interface Port Orientation:**

12-pin Hirose (HR10) **GPIO Connector Type:**

Threading & Mounting

C-Mount **Mount:**

1/4-20 with Tripod Mount Adapter [#89-996](#) **Mounting Threads:**

Environmental & Durability Factors

+5 to +45 **Operating Temperature (°C):**

-10 to +70 **Storage Temperature (°C):**

Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**

Compliant **Reach 240:**

Product Details

- Ideal Analog Replacement
- Up to 1" Maximum Sensors
- Up to 125 fps
- 32MB of Onboard Memory

Allied Vision Manta GigE Cameras are an excellent choice for entry into using the GigE interface. Featuring an intuitive user interface as well as a powerful SDK, these cameras are an excellent value. With options from 0.3 MegaPixels to 12 MegaPixels, all sensors offered cover a wide array of applications. Allied Vision Manta GigE Cameras feature sensors from 1/4" to 1" in size. GigE Cable and Power Supply, both sold separately, are required for operation. Additional [GigE cables](#), [#89-996](#) 1/4-20 Mounting Plate, and [#62-712](#) 12 Pin I/O Cable are available.