

[See all 23 Products in Family](#)

InfiniTube FM-50 (0.25X)

See More by [Infinity Photo-Optical Company](#)



InfiniTube FM-200 (1X), #58-310



Stock **#62-832** **1 In Stock**

A\$1,232⁰⁰

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1+ | A\$1,232.00 each |
| Need More? | Request Quote |

Product Downloads

General

Fixed Magnification Lens **Type:**

Optical Properties

Objective Required **Primary Magnification PMAG:**

Sensor

Maximum Sensor Format:

1/2"

Threading & Mounting

Mount:

C-Mount

Regulatory Compliance

RoHS 2015:

Compliant

Reach 224:

Compliant

Certificate of Conformance:

[View](#)


Product Details

- Direct to Video C-Mount for 2/3" and Smaller Sensor Cameras
- Internal Focusing

InfiniTube™ FM Systems are used to mount infinite-conjugate objectives to C-mount cameras, yielding magnifications not possible with ordinary video lenses, such as 50X magnification. The InfiniTube™ system can be configured in a variety of fashions. It can be utilized alone (InfiniTube™ #58-310 or #58-309) for applications where illumination is provided from another source such as a backlight or directional illumination. The InfiniTube™ FM Systems can also be configured for in-line illumination with attachments. The first in-line attachment (#58-313) has been designed for high performance with objectives having a magnification of 10X or below and is not suggested for use with higher magnification objectives. The second in-line attachment (#58-312) has been designed to work with increased efficiency when used with magnifications of 10X or higher, but can be utilized with all magnifications. All in-line attachments accept our [Fiber Optic Light Guides](#) with a 0.312" tip diameter.

Note: [Standard system](#) for 2/3" sensors still available.

Technical Information



| System Includes | Stock No. |
|--|-------------------------|
| InfiniTube In-Line Assembly Unit | #58-311 |
| Hitachi KP-D20B Camera | #55-837 |
| 15.1" Diagonal LCD Monitor (US version only) | #56-522 |
| Y-C Cable (6 ft.) | #39-255 |
| Mitutoyo/Achrovid™ Objective Adapter | #58-316 |
| M-150 Fiber Optic Illuminator | #55-718 |
| Fiber Optic Light Guide (48" L) | #39-367 |
| Fiber Optic Adapter | #38-944 |
| Standard Boom Stand | #54-120 |
| Rack & Pinion Mounting Plate | #54-123 |
| C-Clamp with 1/4"-20 Mounting Hole | #57-788 |