

[See all 15 Products in Family](#)

Lumenera INFINITY 8-2M Microscopy Monochrome Camera

See More by [Teledyne Lumenera](#)



Stock #25-350 **1 In Stock**

- 1 + A\$3,400⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$3,400.00 each
Need More?	Request Quote

Product Downloads

Monochrome **Spectrum:**

General

Monochrome Microscopy Camera **Type:**

i8-LM00-02M **Model Number:**

Teledyne Lumenera **Manufacturer:**

INFINITY Camera Series:

Physical & Mechanical Properties

41.5 x 45 x 45 (includes lens mount) Dimensions (mm):

108 Weight (g):

Full Housing:

Sensor

128MB Image Buffer:

1" Sensor Format:

1.70 Resolution (Megapixels):

96.00 Frame Rate (fps):

1,608 x 1,104 Pixels (H x V):

9.00 x 9.00 Pixel Size, H x V (µm):

14.47 x 9.94 Sensing Area, H x V (mm):

Sony IMX432 Imaging Sensor:

Progressive Scan CMOS Type of Sensor:

Global Shutter Type:

8/12 bit Pixel Depth:

72 Dynamic Range (dB):

Electrical

2.3 - 3.6 Power Consumption (W):

Hardware & Interface Connectivity

USB 3.1 Interface:

Power over USB Power Supply:

Not Specified GPIOs:

Hardware Trigger (GPIO) Synchronization:

Side Panel Interface Port Orientation:

9-pin Hirose (JST) GPIO Connector Type:

Threading & Mounting

C-Mount Mount:

M3x0.5 (Integrated into Housing) Mounting Threads:

Environmental & Durability Factors

0 to +50 Operating Temperature (°C):

-30 to +70 Storage Temperature (°C):

Regulatory Compliance

[View](#) Certificate of Conformance:

Product Details

- Exceptional Low Light Sensitivity
- Ideal for Life Sciences, Clinical, and Industrial Applications
- Affordable Price Point with Included Microscopy Software



Teledyne
Authorized
Distributor

Teledyne Lumenera INFINITY8 Microscopy Cameras offer an affordable solution for low light imaging in a compact form factor. Featuring low noise and large pixels, these cameras are ideal for a wide range of lighting conditions including the low light levels common in fluorescence imaging. Available with 1/1.8", 2/3", and 1" sensor sizes and megapixel range of 2 – 20 MP, each camera is compatible with Windows and Mac operating systems. Teledyne Lumenera INFINITY8 Microscopy Cameras include an INFINITY ANALYZE 7 software license, for camera operation and immediate analysis of the imaging results, and 3m Micro-B to Type-A USB cable.
