

[See all 78 Products in Family](#)

## Preloaded Norland Optical Adhesive NBA 108H Dispensing Barrel (10cc)

See More by [Norland](#)



10cc Dispensing Barrel for NOA (NOA60 shown as an example)

Stock **#17-384** **2 In Stock**

⊖ 1 ⊕ **A\$63<sup>.20</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1-4	<b>A\$63.20</b> each
Qty 5-11	<b>A\$56.96</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

0.34	<b>Size (oz):</b>
108H	<b>Norland Number:</b>
4 months	<b>Shelf Life:</b>
Barrel	<b>Type:</b>

**Typical Applications:**

Temporary bonding of lenses to metal polishing mounts

**Note:**

Heat curing (-H suffix) adhesives are oxygen inhibited. If used on the surface of a substrate, the adhesive will need to be cured under an inert atmosphere (like nitrogen) to fully cure.

**Optical Properties**

1.51 **Index of Refraction ( $n_d$ ):**

350 - 380 **Absorption Range (nm):**

**Material Properties**

Excellent **Glass Bonding:**

Excellent **Metal Bonding:**

Fair **Plastic Bonding:**

550 **Viscosity (cps):**

Glass to Metal **Bonding Type:**

6 **Energy for Full Cure ( $J/cm^2$ ):**

**Environmental & Durability Factors**

Hard & Resilient **Durability:**

**Regulatory Compliance**

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 251:**

**Product Details**

- Dispensing Syringes Preloaded with 2 or 10g of Adhesive
- Adhesives for Glass, Metal, and Plastic Bonding
- Require a Dispensing Unit & Dispenser Tips for Use
- [Applicator and Bulk Bottles](#) of Norland Adhesive Also Available

Preloaded Norland Optical Adhesive Syringes are pneumatic dispensing syringes preloaded with either 2g or 10g of Norland Optical Adhesive. Norland Optical Adhesives are one-part, UV curing adhesives that are used for glass, metal, and plastic bonding. A range of adhesives are available to meet specific application requirements such as MIL-A-3920 for defense applications, low outgassing for aerospace applications, or UV transmission for UV optical applications. Preloaded Norland Optical Adhesive Syringes require a [dispensing unit](#) and [dispensing tips](#) for use and are ideal for applications requiring precise control of the amount of applied adhesive. Applicators and Bulk Bottles of Norland Adhesive are also available.

**Technical Information**

NORLAND OPTICAL ADHESIVES (NOA) APPLICATION NOTES	
Title	Description
<a href="#">Applying Adhesive</a>	Covers best practices to use when applying Norland Optical Adhesives to ensure an even adhesive layer while avoiding air bubbles.
<a href="#">Chemical Resistance of NOA</a>	Covers the effects of various chemicals on Norland Optical Adhesives including acids, bases, and solvents.
<a href="#">Preventing Lens Separations with NOA</a>	Covers best practices to avoid adhesive failures when bonding optical elements.
<a href="#">Separating Lenses Bonded with NOA</a>	Covers how to unbond optical elements bonded with Norland Optical Adhesives.

