

Ring Light 27mm, 15° Divergence



Stock **#20-181** 2 In Stock

-

1

+

A\$662⁴⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$662.40 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General	
10000	Operating Lifetime (hours):
132	Number of LEDs:

Contents of Kit:
Ring light, mounting plate, retrofit clamp for smaller ID mounting options, diffuser, polarizer, extension

cable	
LED Illuminator	Type of Illumination:
Note: Compatible with EO Lenses: 63-741, 67-310, 63-742, 67-311	
Visionlux Technology	Manufacturer:
Ring Light	
Geometry:	
Physical & Mechanical Properties	
Inner Diameter (mm):	
27.0	
Outer Diameter (mm):	
81.3	
Weight (g):	
241	
Optical Properties	
Color:	
White	
Working Distance (mm):	
63, 83, 105	
Irradiance (W/cm ²):	
16980, 11880, 8860	
Hardware & Interface Connectivity	
Power Supply:	
Power Supply Required and Sold Separately. USA: #15-280 and #73-651 Europe: #73-651	
Regulatory Compliance	
Certificate of Conformance:	
View	

Product Details

- Designed for use with [TECHSPEC® CompactTL™ Telecentric Lenses](#)
- Built-in Cooling Fins for Consistent, High Intensity Performance
- Includes Easy to Integrate Polarizer and Diffuser

LED Ring Lights for Telecentric Lenses provide high intensity and uniform LED illumination with a divergence angle optimized for telecentric lens working distances. Designed to integrate directly with [TECHSPEC® CompactTL™ Telecentric Lenses](#), these ring lights attach without the need for additional custom mounting. Featuring a sturdy metal casing and built in cooling fans, LED Ring Lights for Telecentric Lenses allow for continuous operation over extended periods of time. A mounting plate, clamp, diffuser, polarizer, and extension cable are all included in purchase of a LED Ring Light for Telecentric Lenses.

Note: Power Supply [#73-651](#) is required (sold separately).

Technical Information

RING LIGHT KIT FOR TECHSPEC® COMPACTTL™ AND TECHSPEC® SILVERTL™ TELECENTRIC LENSES (#20-186)		
QTY.	Stock No.	Description
1	#20-177	18mm Inner Diameter, 15 Deg. Divergence
1	#20-178	22mm Inner Diameter, 15 Deg. Divergence
1	#20-179	29.5mm Inner Diameter, 15 Deg. Divergence
1	#20-180	31mm Inner Diameter, 0 Deg. Divergence
1	#20-181	32mm Inner Diameter, 15 Deg. Divergence
1	#20-182	36mm Inner Diameter, 15 Deg. Divergence
1	#20-184	40mm Inner Diameter, 15 Deg. Divergence
1	#20-187	Spotlight
7		Ring Light Diffusers
7		Ring Light Polarizers
12		Compatibility Clamps
1		M12 Extension Cable
1		Controller
1		Power Cord UK
1		Power Cord US
1		Suitcase