

LightPath 354220 | 7.2mm Dia., 0.25 NA, BBAR (350-700nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#87-117** 3-5 DAYS

[Other Coating Options](#)

- 1 +

A\$140.80

ADD TO CART

Qty 1-10

A\$140.80

Qty 11+

A\$124.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
7.20 ±0.020

Effective Focal Length EFL (mm):
11.00 @ 633nm

Numerical Aperture NA:
0.25

Substrate: D-ZK3
Focal Length Tolerance (%): ±1
Aspheric Design Wavelength (nm): 633
Coating: BBAR (350-700nm)
Coating Specification: R _{avg} ≤0.5% @ 350 - 700nm
Surface Quality: 40-20
Clear Aperture CA (mm): 5.5
Edge Thickness ET (mm): 4.21
Center Thickness CT (mm): 5.03 ±0.05
f/#: 2.00
Bevel: Protective bevel as needed
Compatible Window: Thickness: 0.25 (t) (mm) Material: BK7
Distance from Window to Lens (D) (mm): 6.909
Lightpath Lens Code: 354220
Operating Temperature (°C): ≤200
Type: Aspheric Lens
Wavelength Range (nm): 350 - 700
Typical Applications: Collimate or Focus Laser Light
Working Distance (mm): 7.9
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant