

LightPath 354060 | 6.33mm Dia., 0.27 NA, BBAR (600-1050nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Stock **#83-698** 3-5 DAYS
[Other Coating Options](#)

-

1

+

A\$104.00

ADD TO CART

Qty 1-10
A\$104.00
Qty 11+
A\$92.00
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
6.33 ±0.015

Effective Focal Length EFL (mm):
9.60 @ 633nm

Numerical Aperture NA:
0.27

Substrate: D-ZK3
Focal Length Tolerance (%): ±1
Aspheric Design Wavelength (nm): 633
Coating: BBAR (600-1050nm)
Coating Specification: R _{abs} <1.0% @ 600 - 1050nm
Surface Quality: 60-40
Clear Aperture CA (mm): 5.20
Edge Thickness ET (mm): 1.57
Center Thickness CT (mm): 2.49 ±0.05
f/#: 1.85
Bevel: Protective bevel as needed
Lightpath Lens Code: 354060
Type: Aspheric Lens
Wavelength Range (nm): 600 - 1050
Working Distance (mm): 8.100
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant