

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Aspheric Lenses](#) / [Glass Molded](#) / [LightPath® Geltech™ Molded Aspheric Lenses](#)

[See all 91 Products in Family](#)

LightPath 354350 | 4.7mm Dia., 0.43 NA, BBAR (600-1050nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Stock #83-579

Other Coating Options

A\$104.00

A\$104.00

A\$92.00

[Request Quote](#)

Substrate: D-ZK3
Focal Length Tolerance (%): ±1
Aspheric Design Wavelength (nm): 980
Coating: BBAR (600-1050nm)
Coating Specification: R _{abs} <1.0% @ 600 - 1050nm
Surface Quality: 40-20
Clear Aperture CA (mm): 3.7
Edge Thickness ET (mm): 2.77
Center Thickness CT (mm): 3.65 ±0.04
f/#: 1.16
Bevel: Protective bevel as needed
Lightpath Lens Code: 354350
Operating Temperature (°C): ≤200
Type: Aspheric Lens
Wavelength Range (nm): 600 - 1050
Typical Applications: Collimate or Focus Laser Light
Working Distance (mm): 2.2
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant