

0° AOI, 25mm Sq, UV Hot Mirror



UV Hot Mirrors

Stock **#46-588** 3-5 DAYS

- 1 +

A\$232.00

ADD TO CART

Qty 1-9
A\$232.00
Qty 10+
A\$204.80
Volume Pricing
Request Quote

Get Product Downloads

Angle of Incidence (°): 0
Coating: Hot Mirror, 0°
Substrate: ☐ Fused Silica (Corning 7980)
Dimensions (mm):

25.0 x 25.0 ±0.5
Surface Quality: 80-50
Thickness (mm): 3.00
Thickness Tolerance (mm): ±0.2
Type: Shortpass Filter
Clear Aperture (%): 90
Edges: Seamed
Coating Specification: R _{avg} >70% @ 800 - 1050nm T _{avg} >80% @ 245 - 460nm
Wavelength Range (nm): 245 - 1050
Surface Flatness (P-V): 3 - 5λ
Coating Type: Dielectric

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant