


1.05μm, 25mm Diameter, Infrared Longpass Filter



Infrared (IR) Longpass Filters

Stock **#68-651** 3-5 DAYS

-

1

+

A\$476.80

ADD TO CART

Qty 1-9

A\$476.80

Qty 10+

A\$429.12

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
25.00 +0.0/-0.1

Optical Density OD (Average):
≥3.0

Cut-On Wavelength (nm):
1,050.00

Substrate: ☐

Silicon (Si)
Operating Temperature (°C): -62 to +71
Coating: Traditional Coated
Surface Quality: 80-50
Thickness (mm): 1.00
Thickness Tolerance (mm): ±0.2
Transmission (%): >85
Transmission Wavelength (nm): 1100 - 2100
Transmission Wavelength (µm): 1.10 - 2.10
Type: Longpass Filter
Blocking Wavelength Range (nm): 200 - 1050
Parallelism (arcmin): <10
Clear Aperture (%): 90
Slope Factor (%): <12
Cut-On Wavelength (µm): 1.05 ±0.04
Note: Transmission at cut-on wavelength is 5% of peak transmission.
Surface Flatness (P-V): 3 - 5λ

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant