

TECHSPEC® 10mm Dia. x 25mm FL, VIS-NIR, Inked, Achromatic Lens



Stock **#63-719-INK** 10-15 DAYS
[Other Coating Options](#)

- 1 + **A\$140.00**

ADD TO CART

Qty 1-5
A\$140.00
Qty 6+
A\$112.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
10.00 ±0.025

Effective Focal Length EFL (mm):
25.00

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 22.60
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 9.00
Centering (arcmin) : <1
Center Thickness CT (mm) : 5.00 ±0.10
Center Thickness CT 1 (mm) : 3.50 ±0.05
Center Thickness CT 2 (mm) : 1.50 ±0.05
Radius R₁ (mm) : 15.37
Radius R₂ (mm) : -11.10
Radius R₃ (mm) : -31.47
Edge Thickness ET (mm) : 3.76
Substrate : ☐ N-BK7 / N-SF5
Surface Quality : 40-20
f/# : 2.5
Numerical Aperture NA : 0.20
Coating : VIS-NIR (400-1000nm)
Coating Specification : R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 400 - 1000

Regulatory Compliance

RoHS : Compliant
Certificate of Conformance : View