

TECHSPEC® 10mm Dia. x 20mm FL, VIS 0° Coated, Double-Convex Lens



Stock **#63-601**

3-5 DAYS

[Other Coating Options](#)



1



A\$64.80

ADD TO CART

Qty 1-9

A\$64.80

Qty 10+

A\$58.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
10.00 +0.0/-0.025

Back Focal Length BFL (mm):
19.16

Effective Focal Length EFL (mm): 20.00
Coating: VS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 2.50
Center Thickness Tolerance (mm): ±0.05
Edge Thickness ET (mm): 1.25
Radius R₁=R₂ (mm): 20.24
Clear Aperture CA (mm): 9
f/#: 2.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.25
Type: Double-Convex Lens
Wavelength Range (nm): 425 - 675
Damage Threshold, Reference: ☐ 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant