

TECHSPEC[®] 10mm Dia. x 25mm FL, VIS-NIR Inked, Double-Convex Lens



Stock **#63-666-INK** 10-15 DAYS
[Other Coating Options](#)

-

1

+

A\$84.80

ADD TO CART

Qty 1-9
A\$84.80
Qty 10+
A\$76.40
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
10.00 ±0.025

Back Focal Length BFL (mm):
24.16

Effective Focal Length EFL (mm): 25.00
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870 nm R _{avg} ≤1.25% @ 890 - 1000nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 2.50
Center Thickness Tolerance (mm): ±0.05
Edge Thickness ET (mm): 1.51
Radius R₁=R₂ (mm): 25.41
Clear Aperture CA (mm): 9.00
f/#: 2.5
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.20
Type: Double-Convex Lens
Wavelength Range (nm): 400 - 1000
Damage Threshold, By Design: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View