

TECHSPEC[®] 12.0mm Diameter x 24.0mm FL, 980nm V-Coat, PCX Lens



633nm Laser Line Coated Plano-Convex (PCX) Lenses

Stock **#69-553** CLEARANCE 3-5 DAYS

[Other Coating Options](#)



1



A\$33.52

ADD TO CART

Qty 1+

A\$33.52

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
12.00 +0.0/-0.025

Effective Focal Length EFL (mm):
24.00 @ 587.6nm

Back Focal Length BFL (mm):
22.15

Coating:
Laser V-Coat (980nm)

Coating Specification: R_{abs} <0.25% @ 980nm
Substrate: N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 2.80 ±0.05
Edge Thickness ET (mm): 1.25
Radius R₁ (mm): 12.42
Clear Aperture CA (mm): 11
f/#: 2.00
Numerical Aperture NA: 0.25
Design Wavelength DWL (nm): 980
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Damage Threshold, By Design: 5 J/cm² @ 980nm, 10ns

Regulatory Compliance

RoHS: Compliant
Reach 224: Compliant
Certificate of Conformance: View