

TECHSPEC® 12.5mm Dia x -75mm FL VIS 0° Coated, Negative Achromatic Lens



Stock **#62-489** 3-5 DAYS

[Other Coating Options](#)

- 1 + **A\$140.80**

ADD TO CART

Qty 1-5
A\$140.80
Qty 6+
A\$119.68
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.025

Effective Focal Length EFL (mm):
-75.00

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : -77.47
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 11.50
Centering (arcmin) : <1
Center Thickness CT (mm) : 5.50 ±0.10
Center Thickness CT 1 (mm) : 2.50 ±0.05
Center Thickness CT 2 (mm) : 3.00 ±0.05
Radius R₁ (mm) : -46.07
Radius R₂ (mm) : 36.65
Radius R₃ (mm) : 108.00
Edge Thickness ET (mm) : 6.05
Substrate : ☐ N-BK7 / N-SF5
Surface Quality : 40-20
f/# : 6.00
Numerical Aperture NA : 0.08
Coating : VIS 0° (425-675nm)
Coating Specification : R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Negative Achromatic Lens
Wavelength Range (nm) : 425 - 675

Regulatory Compliance

RoHS 2015 : Compliant
Reach 219 : Compliant
Certificate of Conformance : View