

TECHSPEC®

1.5mm Dia. x 2.0mm FL, VIS 0° Coated, Plano-Convex Lens



Stock **#65-279** 3-5 DAYS

[Other Coating Options](#)

-

1

+

A\$124.00

ADD TO CART

Qty 1-9
A\$124.00
Qty 10+
A\$111.60
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
1.50 +0.0/-0.025

Effective Focal Length EFL (mm):
2.00 @ 587.6nm

Back Focal Length BFL (mm): 1.57
Coating: VS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Substrate: ☐ N-LASF9
Surface Quality: 20-10
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): 30-45, typical
Center Thickness CT (mm): 0.80 ±0.05
Edge Thickness ET (mm): 0.63
Radius R₁ (mm): 1.70
Clear Aperture CA (mm): 1
f/#: 1.33
Numerical Aperture NA: 0.38
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 425 - 675
Damage Threshold, By Design: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant