

TECHSPEC® 15mm Dia., 0.50 Numerical Aperture Uncoated, Aspheric Lens



Stock **#47-726** 3-5 DAYS

[Other Coating Options](#)

- 1 +

A\$360.00

ADD TO CART

Qty 1-5

A\$360.00

Qty 6+

A\$288.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
15.00 +0.0/-0.1

Effective Focal Length EFL (mm):
15.00 @ 587.6nm

Numerical Aperture NA:
0.50

Back Focal Length BFL (mm): 11.54
Substrate: L-BAL35
Aspheric Design Wavelength (nm): 587.6
Asphere Figure Error, RMS @ 632.8nm: 1.2λ
Coating: Uncoated
Centering (arcmin): ≤5
Surface Quality: 60-40
Clear Aperture CA (mm): 13.5
Edge Thickness ET (mm): 2.04
Center Thickness CT (mm): 5.50 ±0.1
f#: 1.00
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 330 - 2400
Conjugate Distance: Infinite
Power (diopters): 66.67

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View